

**HOLEX****Hook turning tool right-hand, similar to DIN 263 (ISO 11), M20, Shank square: 20mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 297145 20     |
| GTIN         | 4045197885623 |
| Item class   | 22E           |

**Description****Version:**

Fitted with diamond ground carbide inserts.

**Application:**

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

**Attention:**

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

**Technical description**

|                                   |              |
|-----------------------------------|--------------|
| Shank square                      | 20 mm        |
| maximum grooving depth $t_{\max}$ | 16 mm        |
| for bores from $\varnothing$      | 50 mm        |
| Blade width                       | 6 mm         |
| Overall length                    | 210 mm       |
| Tool material                     | M20          |
| Type of product                   | Turning tool |