



Hook turning tool right-hand, similar to DIN 263 (ISO 11), M20, Shank square: 20mm



Order data

Order number	297145 20
GTIN	4045197885623
Item class	22E

Description

Version:

Fitted with diamond ground carbide inserts.

Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Overall length: 210 mm

Blade width: 6 mm

for bores from \varnothing : 50 mm

maximum grooving depth t_{max} : 16 mm

Technical description

Shank square	20 mm
maximum grooving depth t_{max}	16 mm
for bores from \varnothing	50 mm
Blade width	6 mm
Overall length	210 mm
Tool material	M20
Type of product	Turning tool

