

HOLEX

Grooving tool right-hand, similar to DIN 4981 (ISO 7), M20, Shank height: 32mm



Order data

Order number	297030 32
GTIN	4045197885579
Item class	22E

Description

Version:

Fitted with diamond ground carbide inserts.

Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Technical description

Shank height h	32 mm
Blade width	8 mm
Overall length	170 mm
Shank width b	20 mm
Tool material	M20
Type of product	Turning tool