

**Garant****Table trolley with height-adjustable platform TA9, Type: TA94****Order data**

Order number	918557 TA94
GTIN	4045197885326
Item class	91T

**Description****Version:**

Welded steel construction, platform of chipboard with anthracite-coloured scratch-resistant surface. **Height is adjustable manually** by means of a hand crank. By this means the platform can be moved up and down with **4 mechanical spindle lifting pillars**. Handle of impact-resistant polypropylene with a Haptoprene® insert, this can be swung up in order to operate the hand crank. 2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

**Colour:**

Silver and anthracite **powder-coated**.

**Note:**

For reasons of safety no perforated panel can be fitted.

**Technical description**

Platform area depth	600 mm
Wheel Ø	200 mm
Platform area width	1040 mm
Type	TA94

maximum load capacity	400 kg
Height of bottom shelf	270 mm
Height adjustment range	760 - 1080 mm
Weight	88.2 kg
Width	1220 mm
Load capacity of top shelf	200 kg
Depth	609 mm
Type of product	Table trolleys