




Flap wheel (SiC), 80 grit, Head Ø×head width: 60X30mm



Order data

Order number	554660 60X30
GTIN	4045197240996
Item class	52E

Description

Version:

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **silicon carbide grit (SiC)**. Shank Ø 6 mm.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Technical description

Grit	80
recommended speed	8000 min ⁻¹
Head width	30 mm
maximum speed	12700 min ⁻¹
Shank Ø	6 mm
Head Ø	60 mm
Grinding media	Silicon carbide (SiC)
Grinding medium code	SiC

Product name attribute	80 grit
Type of product	Flap wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable only under restricted conditions		
dry	suitable		