

**KERN**
**Hanging scales type HCB, maximum weighing range: 500kg**

**Order data**

Order number	479435 500
GTIN	4045761144460
Item class	47D

**Description**
**Version:**

- **Simple operation with 3 buttons.**
- **With tare button, attach empty container and set indication to zero.**
- **Hold button, the indication can be frozen for 5 seconds.**
- **Display unit switchable between kg, N and lb.**

**Supplied with:**

Stainless steel carabiner, stainless steel S-hook (non-standard for size 500 / 1000) and 3 batteries No.081561 size LR6.

**Optional extras:**

Shackle and hook with safety lock on request.

**Technical description**

Body depth	42 mm
Body height	152 mm
Calibration	Price on request
Scale divisions	1000 g

Net weight	0.35 kg
Body width	80 mm
maximum weighing range	500 kg
Number of batteries contained	3
Article no of the battery / rechargeable battery fitted	081561 LR6
Power supply	Battery-powered
Manufacturer's designation	HCB
Type of product	Suspended scales / crane scales

---

## Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------