




## KF 708 fibre disc fused aluminium oxide (A), Ø 125 mm, Grit: 16



### Order data

|              |               |
|--------------|---------------|
| Order number | 566500 16     |
| GTIN         | 4018875993163 |
| Item class   | 56V           |

### Description

#### Version:

Tear-resistant but very flexible **vulcanised fibre**. Bore diameter 22.23 mm and crossed slots.

**VSM KF 708 high-quality universal fibre disc** for grinding metals, plastic, wood etc. Grit type:

**Fused aluminium oxide (A).**

#### Application:

Limited to maximum 80 m/s circumferential speed with backing pads No. 566650 / 566670 on angle grinders. For **grinding flat and curved surfaces** with a high degree of **flexibility**.

### Technical description

|                            |                           |
|----------------------------|---------------------------|
| Manufacturer's designation | VSM KF 708                |
| Grit                       | 16                        |
| Disc Ø                     | 125 mm                    |
| Series                     | KF708                     |
| Grinding media             | Fused aluminium oxide (A) |
| Grinding medium code       | A                         |
| Grinding media backing     | Vulcanised fibre          |

|   |                            |
|---|----------------------------|
| Iron, sulphur and chlorine constituents | < 0.1 %                    |
| Product name attribute                  | Ø 125 mm                   |
| Adapter                                 | Roloc™ quick-change system |
| Bore Ø                                  | 22.23 mm                   |
| suitable for quick-change system        | Roloc™                     |
| optimised for material                  | Steel                      |
| maximum circumferential speed           | 80 m/s                     |
| maximum speed                           | 12200 min <sup>-1</sup>    |
| Type of product                         | Fibre disc                 |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable only under restricted conditions |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| Steel < 67 HRC                 | suitable only under restricted conditions |                |          |
| INOX                           | suitable only under restricted conditions |                |          |
| Ti                             | suitable only under restricted conditions |                |          |
| GG(G)                          | suitable only under restricted conditions |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable                                  |                |          |
| Wood                           | suitable                                  |                |          |
| dry                            | suitable                                  |                |          |

---

## Accessories

|   |            |
|---|------------|
| ISO backing padflexible/smooth External Ø 117 mm    | 566650 117 |
| Backing padhard/ribbed External Ø 125 mm            | 566672 125 |
| ISO backing padmedium hard/ribbed External Ø 117 mm | 566670 117 |