

KERN
Counting system, type CCS, maximum weighing range: 60kg


Order data

Order number	479542 60
GTIN	4045761153288
Item class	47D

Description

Version:

- **Precision counting scales with automatic reference optimisation (progressive refinement of the average value of the item weight).**
- **Target item count and target weight programmable to give an acoustic signal.**
- **Cumulative item counter for totalling identical items by total quantity and overall weight.**
- **Reference quantities or reference weight.**
- **Selectable mains and battery operation.**
- **CAL calibration programme: For calibrating the accuracy (requires an external calibration weight which is available on request).**
- **Display switching between items and weight.**

Counting system consisting of **reference scales and quantity scales (platform scales)** with a 2.0 m connection cable.

Supplied with:

Mains adapter 230 V/ 50 Hz and protective hood for reference scales.

Optional extras:

Internal battery, signal lamp available on request.

Note:

For calibration please select both the items offered, since both the reference scales and also the quantity scales (platform scales) must be calibrated.

Technical description

Settling time	2 s
Depth	350 mm
Platform scales depth	400 mm
maximum weighing range	0 - 60 kg
Minimum unit weight	1 g
Width	320 mm
Linearity	±0.2 g
Platform scales width	500 mm
Platform scales height	137 mm
Reproducibility	0.1 g
Scale divisions	0.1 g
Net weight	13 kg
Height	125 mm
Dimensions of weighing plate	294×225 mm
Reading the quantity scales	2 g
Power supply	Rechargeable battery-powered
Calibration	Price on request
Type of product	Counting balance