




Smooth rolling tool EG45-40M universal, Shank mounting type: VDI40



Order data

Order number	291520 VDI40
GTIN	4060491000190
Item class	29F

Description

Version:

For use on CNC and conventional lathes.
With symmetrical structure – can be used universally as right-hand or left-hand version.

Advantage:

Surface quality $R_z < 1 \mu\text{m}$ possible.
Feed rates up to 1 mm/rev possible (external machining).
Consistent results due to continuous measurement of the rolling force.

Application:

For mechanical surface finishing.
For machining all metallic materials up to a tensile strength of 1400 N/mm^2 and a hardness of up to 45 HRC.

Suitable for:

Ø range (recommended): from 35 mm

Recommendation:

For external surfaces with subsequent radius up to plane surface.

Note:

- **Other shank connections on request.**
- **Detailed technology recommendations can be found in the instruction manual.**

Roller radius = 2.5 mm. Machinable workpiece radii from 4 mm to 12 mm.

Technical description

maximum rolling force	4 kN
Roll \varnothing	40 mm
Tip centre offset f	69 mm
Shank mounting type	VDI40
Overhang L _A	129 mm
Cutting direction	Left-hand and right-hand
Type of product	Smooth rolling tool