




## Flap wheel (SiC), 150 grit, Head Ø×head width: 60X30mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 554680 60X30  |
| GTIN         | 4045197241023 |
| Item class   | 52E           |

### Description

#### Version:

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **silicon carbide grit (SiC)**. Shank Ø 6 mm.

#### Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

### Technical description

|                      |                         |
|----------------------|-------------------------|
| Head width           | 30 mm                   |
| Grit                 | 150                     |
| recommended speed    | 8000 min <sup>-1</sup>  |
| maximum speed        | 12700 min <sup>-1</sup> |
| Shank Ø              | 6 mm                    |
| Head Ø               | 60 mm                   |
| Grinding media       | Silicon carbide (SiC)   |
| Grinding medium code | SiC                     |

|                        |            |
|------------------------|------------|
| Product name attribute | 150 grit   |
| Type of product        | Flap wheel |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| Steel < 67 HRC                 | suitable only under restricted conditions |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable only under restricted conditions |                |          |
| GG(G)                          | suitable                                  |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable                                  |                |          |
| Stone                          | suitable only under restricted conditions |                |          |
| Paint                          | suitable only under restricted conditions |                |          |
| dry                            | suitable                                  |                |          |