

HOLEX**Flap wheel for stainless steel, 150 grit, Head Ø×head width: 60X30mm****Order data**

| | |
|--------------|---------------|
| Order number | 554410 60X30 |
| GTIN | 4045197377678 |
| Item class | 52E |

Description**Version:**

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **Aluminium Oxide (A)**. With **active abrasive bonding** for stainless steels

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Technical description

| | |
|-------------------|--------------------------|
| Grit | 150 |
| maximum speed | 12700 min ⁻¹ |
| recommended speed | 8000 min ⁻¹ |
| Head width | 30 mm |
| Shank Ø | 6 mm |
| Head Ø | 60 mm |
| Grinding media | Aluminium Oxide grit (A) |

| | |
|------------------------|------------|
| Grinding medium code | A |
| Product name attribute | 150 grit |
| Type of product | Flap wheel |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable only under restricted conditions | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| dry | suitable | | |