




Flap wheel brush (A), 240 grit, Head \varnothing ×head width: 40X20mm



Order data

Order number	554800 40X20
GTIN	4045197241054
Item class	52E

Description

Version:

Flap strips bonded on to the shank of the tool.
Flap wheel with multiple slits in each strip. Shank \varnothing 6 mm.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component. Highly recommended for sanding contoured surfaces.

Technical description

Head width	20 mm
Grit	240
recommended speed	12000 min ⁻¹
maximum speed	19100 min ⁻¹
Shank \varnothing	6 mm
Head \varnothing	40 mm
Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A

Product name attribute	240 grit
Type of product	Flap wheel

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable only under restricted conditions		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		