

**Cupped flap wheel (A), 80 grit, Head Ø×head width: 60X40mm****Order data**

Order number	555010 60X40
GTIN	4045197241283
Item class	52E

**Description****Version:**

Flap strips bonded on to the shank of the tool.

**Cup shaped strip arrangement** around the shank of the tool, with recessed core. Shank Ø 6 mm.

**Application:**

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component. Particularly suitable for peripheral and internal face grinding.

**Technical description**

Head width	40 mm
Grit	80
maximum speed	12000 min <sup>-1</sup>
recommended speed	8000 min <sup>-1</sup>
Shank Ø	6 mm
Head Ø	60 mm
Grinding media	Aluminium Oxide grit (A)

Grinding medium code	A
Product name attribute	80 grit
Type of product	Flap wheel

**User data**

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		