



## SENSOTORK® workshop torque analyser, maximum torque: 20N·m



### Order data

Order number	654250 20
GTIN	4018754181148
Item class	63B

### Description

#### Version:

#### Compact workshop torque analyser for torque wrenches.

Flexible extension by exchanging the measurement transducer. High accuracy due to flat measurement transducers (low lateral forces) with measured value post-processing and digitising directly within the measurement transducer (deviation from measured value is  $\pm 0.25\%$  in the range from 20 % - 100 % of the nominal value;  $\pm 0.5\%$  in the range from 10 % - 20 % of the nominal value and  $\pm 1\%$  in the range from 2 % - 10 % of the nominal value).

High security due to additional display of the actual torque applied when testing triggering torque wrenches.

#### Supplied with:

Measurement transducer, retainer, display, support for display, flexible coiled cable, mains adapter, 1.5 m connection cable, fixing kit for horizontal and vertical checking positions.

### Technical description

Dimension $h_2$	215 mm
Dimension $h_1$	79 mm
maximum torque	20 Nm

Dimension b	180 mm
Dimension l	180 mm
Weight	6.2 kg
Square socket	1/4 in
Measuring range	0.4 – 20 Nm
Power supply	Mains operated
Direction of tightening	For right and left-hand tightening
Interface	USB interface
Test certificate	Manufacturer's test certificate
Calibration	O4
Type of product	Calibration and adjustment device

## Services

Calibration clockwise / anti-clockwise Torque analyser / sensor maximum torque 400/2 N·m	020140 400/2
DAkkS calibration clockwise / anti-clockwise Torque analyser / sensor maximum torque 0,1-1100/2 N·m	020150 0,1-1100/2

## Accessories

Measurement transducer maximum torque 20 N·m	654255 20
--	-----------