

**Carbide granulate disc, Disc Ø: 115mm****Order data**

Order number	569610 115
GTIN	4027497070534
Item class	53L

**Description****Version:**

Steel disc with brazed-on carbide grit. Very long working lives and **extremely high metal removal rates**; medium grit.

**Application:**

Grinding, correcting, trimming GFRP, calcareous sandstone, plaster board, aerated concrete, rubber. Also for smoothing rough formwork edges on exposed concrete.

**Note:**

Not for use on metal. Work with low contact force. Avoid impact loads. Maximum speed 63 m/s (10,500 rpm.)

**Technical description**

Bore Ø	22.23 mm
maximum speed	10500 min <sup>-1</sup>
Disc Ø	115 mm
Grinding media	Carbide granulate
Shape description	dished

Backing pad	Steel disc
optimised for material	Stone
optimised for material	Plasterboard
optimised for material	Rubber
optimised for material	Fibre-reinforced plastics
Propulsive equipment	Angle grinder
maximum circumferential speed	63 m/s
Type of product	Cutting disc