



## Flange mounted transducer "FMT", maximum torque: 2N·m



### Order data

Order number	654350 2
GTIN	5060922232892
Item class	66D

### Description

#### Version:

- **Static sensors complete with cable (2 m) for direct connection to No. 654300 or No. 654340 (automatic detection of calibration data).**
- **Direct fixing to the workbench with 3 screws (not included).**

#### Supplied with:

#### **UKAS calibration certificate on the right.**

Up to and including size 150 with screw tightening simulator for checking electric and pneumatic screwdrivers. In a sturdy plastic case.

#### **Note:**

Not suitable for impact wrenches.

### Technical description

maximum torque	2 Nm
Square socket	1/4 in
Measuring range	0.04 - 2 Nm
Hexagon socket	1/4 in
Calibration	O4
Direction of tightening	Right-hand tightening
Torque measuring accuracy	± 0.5 %
Test certificate	Manufacturer's test certificate

Type of product

Torque testing device

---

**Services**

Calibration, clockwiseTorque analyser / sensor Type 400

020120 400

---

**Accessories**

Screw tightening simulator maximum torque 2 N·m

654352 2