



Flange mounted transducer "FMT", maximum torque: 150N·m



Order data

Order number	654350 150
GTIN	5060922233035
Item class	66D

Description

Version:

- **Static sensors complete with cable (2 m) for direct connection to No. 654300 or No. 654340 (automatic detection of calibration data).**
- **Direct fixing to the workbench with 3 screws (not included).**

Supplied with:

UKAS calibration certificate on the right.

Up to and including size 150 with screw tightening simulator for checking electric and pneumatic screwdrivers. In a sturdy plastic case.

Note:

Not suitable for impact wrenches.

Technical description

maximum torque	150 Nm
Measuring range	7.5 - 150 Nm
Square socket	3/8 in
Square socket	1/2 in
Calibration	O4
Direction of tightening	Right-hand tightening

Torque measuring accuracy	± 0.5 %
Test certificate	Manufacturer's test certificate
Type of product	Torque testing device

Services

Calibration, clockwiseTorque analyser / sensor Type 400	020120 400
DAkkS calibration, clockwiseTorque analyser / sensor Type 1000	020130 1000
DAkkS calibration clockwise / anti-clockwiseTorque analyser / sensor maximum torque 1000/2 N·m	020150 1000/2

Accessories

Screw tightening simulator maximum torque 150 N·m	654352 150
---	------------