



Arbor for screw-in milling cutters with thread, SK 40, Thread M × Length L1: M10X75



Order data

Order number	301308 M10X75
GTIN	4045197871664
Item class	31A

Description

Version:

Tapered design.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Pull studs (PS) No. 308600 - 308806, PS wrenches No. 308810– 308830.

Arbor standard: ISO 7388-1

Arbor standard: DIN 69871

Shape: ADB

Balance quality G at rotational speed: G 2.5 at 25,000 rpm

Concentricity: $\leq 3 \mu\text{m}$

Machining strategy: HSC

Overhang dimension A: 94 mm

Bore $\varnothing D_1$ tolerance IT6: 10.5 mm

$\varnothing D_2$: 18 mm

External $\varnothing D$: 23 mm

Reach L_1 : 75 mm

L_2 : 5 mm

Technical description

Thread M	M10×75
L_2	5 mm

Overhang dimension A	94 mm
Reach L ₁	75 mm
Ø D ₂	18 mm
Bore Ø D ₁ tolerance IT6	10.5 mm
External Ø D	23 mm
Capacity	SK 40
Arbor standard	ISO 7388-1
Arbor standard	DIN 69871
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC

Accessories

Pull stud sealed, form A suitable for steep tapers 30	308610 30
Pull-stud 90° sealed suitable for steep tapers 50	308790 50
Torque insert for Pull studs to DIN 69872 suitable for steep tapers 50 SK	308810 50
Pull stud sealed suitable for steep tapers 50	308660 50
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 40 SK	308830 40
Special pull-stud with no internal thread sealed suitable for steep tapers 40	308720 40
Special pull-stud with no internal thread sealed suitable for steep tapers 50	308700 50
Pull stud sealed, form B suitable for steep tapers 40	308650 40
Pull stud Form B suitable for steep tapers 50	308640 50

Pull stud stud sealed, form A suitable for steep tapers 40	308610 40
Pull-stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 50 SK	308820 50
Pull stud Hurco 60° with fit sealed suitable for steep tapers 40	308804 40
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 50	308615 50
Pull-stud 60° sealed suitable for steep tapers 50	308780 50
Pull-stud 60° sealed suitable for steep tapers 50	308785 50
Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 50 SK	308830 50
Pull stud sealed, form B suitable for steep tapers 40	308620 40
Pull-stud 60° sealed suitable for steep tapers 40	308785 40
Pull-stud 45° sealed suitable for steep tapers 40	308760 40
Hurco 60° pull stud with bore and fit sealed suitable for steep tapers 40	308803 40
Pull-stud 60° sealed suitable for steep tapers 30	308780 30
Pull stud sealed suitable for steep tapers 40	308660 40
Pull stud stud sealed, form A suitable for steep tapers 50	308610 50
Pull-stud 60° sealed suitable for steep tapers 40	308780 40
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
Pull-stud 45° sealed suitable for steep tapers 50	308760 50
Pull stud sealed, form B suitable for steep tapers 50	308620 50
Torque insert for Pull studs to SO 7388 suitable for steep tapers 50 SK	308812 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 40 SK	308820 40

Pull-stud 45° sealed suitable for steep tapers 30	308760 30
Pull-stud 45° sealed suitable for steep tapers 30	308765 30
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
Pull-stud 90° sealed suitable for steep tapers 40	308790 40
Pull stud Form A suitable for steep tapers 40	308600 40
Special pull-stud with no internal thread sealed suitable for steep tapers 50	308720 50
Pull-stud 45° sealed suitable for steep tapers 50	308765 50
Pull stud Form B suitable for steep tapers 40	308640 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
Pull-stud 90° sealed suitable for steep tapers 50	308795 50
Pull-stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud Mazak sealed, form A suitable for steep tapers 40M	308670 40M
Pull stud Hurco 90° with bore and fit sealed suitable for steep tapers 40	308805 40
Torque insert for Pull studs to DIN 69872 suitable for steep tapers 40 SK	308810 40
Torque insert for Pull studs to SO 7388 suitable for steep tapers 40 SK	308812 40
Pull stud sealed suitable for steep tapers 40	308635 40
Pull stud sealed, form B suitable for steep tapers 50	308650 50
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 50	308605 50
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40	308605 40
Pull stud Form A suitable for steep tapers 50	308600 50
Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40	308801 40
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull-stud 60° sealed suitable for steep tapers 30	308785 30

Special pull-stud with no internal thread sealed suitable for
steep tapers 40

308700 40