

3M Scotch-Brite™

Compact disc RC-UW Rapid Cut W × D × H (mm), 150×6×25, Grit equivalent: 100**Order data**

Order number	566994 100
GTIN	50051141539848
Item class	53M

Description**Version:**

Compact disc of compressed fibre fleece for cool grinding without discolouration.

Rapid Cut compact discs combine **aggressive Cubitron™ II** precision grit with Scotch-Brite™ fibre fleece.

Application:

For **dressing, cleaning and finishing** of fillet welds, weld spatter and inaccessible places using straight die grinders (Ø 76 mm), angle grinders (Ø 125 mm) or fillet weld grinding machines (Ø 150 mm).

No further accessories required for use on fillet weld grinding machines.

Note:

Fleece compact wheels for surface grinding can be found under No. 566991. Deburring and finishing wheels for use on bench grinders can be found under No. 568725, No. 568731 and No. 568741.

Iron, sulphur and chlorine constituents: < 0.1 %

maximum circumferential speed: 60 m/s

maximum speed: 7500 rpm

Grinding medium code: Ceramic

Grit designation: coarse

Degree of hardness: extra hard

Version: 9C coarse

Technical description

Version	9C coarse
Grit equivalent	100
Degree of hardness	extra hard
Grit designation	coarse
Disc Ø D	150 mm
Bore Ø H	25 mm
Disc thickness T	6 mm
Grinding medium code	Ceramic
Grinding media	Ceramic grit (CER)
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	150×6×25
Manufacturer's designation	RC-UW Rapid Cut
maximum circumferential speed	60 m/s
maximum speed	7500 rpm