

3M
Mini-linishing belt Ø 90×100 mm, 237AA, Grit: 240

Order data

Order number	568550 240
GTIN	4001895606458
Item class	53M

Description
Version:

Mini-belts Ø 90×100 mm (289×100 mm).

The fine-structured pyramidal surface guarantees the **best finish and very long working life**. Particularly suitable for the intermediate grinding of stainless steel sheets.

Application:

For use on surface grinding and burnishing machines with backing rollers No. 568570 / 568575 (mounting bore Ø 19 mm). Maximum speed 5000 rpm.

Grinding medium code: A

Iron, sulphur and chlorine constituents: < 0.1 %

3M grit designation: A080

Technical description

Linishing belt Ø	90 mm
3M grit designation	A080
Linishing belt width	100 mm
Grit	240
Grinding medium code	A

Iron, sulphur and chlorine constituents	< 0.1 %
Manufacturer's designation	237AA

Accessories

Backing roller Ø 90×100 mm Type SOFT	568580 SOFT
--------------------------------------	-------------