



Combination spanner, Width across flats: 38mm



Order data

Order number	613500 38
GTIN	4018754019014
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw width.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Ring end with **AS-Drive** profile. (Sizes 3.2 – 5 with hexagon).

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Note:

AS-Drive – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **AS-Drive** symbol.

Advantage:

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Spanner length L: 480 mm

maximum jaw height h₁: 11 mm

maximum ring height h_{2_max}: 19 mm

Technical description

Width across flats	38 mm
Spanner length L	480 mm
maximum jaw height h ₁	11 mm
Width across flats	metric

maximum ring height $h_{2\max}$	19 mm
Standard	DIN 3113 A
Standard	ISO 3318
Standard	ISO 7738
Ring setting	15°
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chromium-plated over nickel
Type of product	Spanner