

**Spring balance, maximum measuring range: 100CN****Order data**

Order number	478900 100CN
GTIN	4045197208118
Item class	42H

**Description****Version:**

Sturdy metal housing in practical design; hammer finish. Clear dial face with double scale for measuring in both directions. With pointer and memory pointer.

**Application:**

For electrical engineering and fine mechanical work, e.g. setting the contact pressure of relay springs, checking the brush pressure on motors or for adjusting tension or compression springs.

**Accuracy:**

$\pm 0.01 \times (\text{measuring range} + \text{measured value})$ .

Calibration: K1

Measuring range: 0.1 - 1 N

Scale graduations: 2 cN

Probe length L: 29 mm

Dial face Ø: 36 mm

**Technical description**

Measuring range	0.1 - 1 N
Probe length L	29 mm
Dial face Ø	36 mm
Scale graduations	2 cN
Calibration	K1

Measurement technology	analogue
Type of product	Spring balance

## Services

Labelling laser-etched Type	018940
Calibration Spring balance	018870
Calibration Spring balance Type F	027730 F