

3M Scotch-Brite™

Abrasive fleece pad, 158×224 mm, Fleece structure: 100**Order data**

Order number	556000 100
GTIN	3134375444491
Item class	53M

Description**Version:**

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding.

Advantage:

- **Adapts to the shape of the component.**
- **The open structure prevents clogging and reduces heat development.**
- **Consistent reproducible finish.**
- **Can be used wet or dry.**
- **Contains no materials that could cause corrosion.**

Application:

Can be used by hand, on hand block No. 556020 or on an orbital sander. **Coarse and aggressive:** removes rust, rust film, and surface soiling. For roughening old paint, varnish, plastics, rubber parts (e. g. prior to bonding).

Technical description

Fleece structure	100
Colour	red
Grit equivalent	180 - 220
Grit designation	coarse
3M designation	WR-SH
Version	A Medium
Iron, sulphur and chlorine constituents	< 0.1 %

Width	158 mm
Length	224 mm
Product name attribute	158x224 mm
Type of product	Abrasive fleece pad

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		

Accessories

Mandrel	556030
---------	--------

Hand block

556020