



## 4 in1 diamond cutting disc PREMIUM\*\*\* Premium, Disc Ø: 230 mm



### Order data

Order number	569735 230
GTIN	9003177046179
Item class	53T

### Description

#### Version:

Diamond cutting discs for wet and dry cutting. Bore Ø 22.23 mm.

- **High cutting performance of diamonds gives short cutting times.**
- **Extremely long working life, fewer disc changes.**
- **Unvarying diameter, always cuts to the full depth.**
- **Hardly any disc wear, reducing dust generation.**

**Maximum performance and working life** due to new segment technology with optimised grit distribution. 20 – 30 % faster cutting with **less vibration and clean cut edges**. For **general-purpose use** on concrete, granite, abrasive materials, and reinforced concrete. **Coating height 14 mm.**

#### Standard:

Diamond cutting discs for **wet and dry cutting**. Bore Ø 22.23 mm.

**Maximal performance and working life;** clean cut edges. For **general-purpose use** on concrete, granite, abrasive materials and steel.

#### Application:

For cutting all common building materials such as concrete (even reinforced), bricks, natural stone, tiles, ceramics, steel etc.

#### Note:

- **Diamond coating already pre-sharpened. Observe correct direction of rotation!**
- **Other diamond cutting discs on request.**

maximum circumferential speed: 80 m/s

Bore Ø: 22.23 mm

Bore Ø: 22.23 mm

---

## Technical description

Bore Ø	22.23 mm
Abrasive coating height	14 mm
Disc Ø	230 mm
maximum speed	6600 rpm
Grinding media	Diamond
Grinding medium code	D
Shape	41
Shape description	straight
maximum circumferential speed	80 m/s
Type of product	Cutting-off wheel