

**Garant****CNMG 09T304, Grade: HB7035-1**

## Order data

Order number	250150 HB7035-1
GTIN	4045197873811
Item class	21G

## Description

CN.G 09T304 HB7035-1 Grade: HB7035-1  
Chip breaker: SM  
Tolerance: M  
Cutting depth  $a_p$ : 0.5 - 8 mm  
Feed  $f$ : 0.2 - 0.5 mm/rev.  
Cutting speed  $v_c$  main application: 100 - 320 m/min

## Technical description

Main application	P
Chip breaker	SM
Corner radius	0.4 mm
Cutting depth $a_p$	0.5 - 8 mm
Cutting conditions	heavily interrupted
Grade	HB7035-1

Feed f	0.2 - 0.5 mm/rev.
Cutting speed $v_c$ main application	100 - 320 m/min
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	CNMG 09T304
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning