

LESSMANN®
THE GERMAN BRUSH COMPANY
**Wire wheel brush Steel wire 0.30 / 0.35 mm, Brush Ø D1× bristle width L1:
 178X32mm**

Order data

Order number	570100 178X32
GTIN	4017359004982
Item class	57L

Description
Version:

Waved wire firmly crimped into the steel body. **High density**, high concentricity, and good wear resistance. Adaptable to various different mounting bores by use of **interchangeable reducing rings** (supplied).

Application:

Use on bench grinder or polishing machines, or on machines with flexible drive heads. For roughening, cleaning, removing rust, and scale etc.

Technical description

Length of brush section H ₁	37 mm
Brush Ø D ₁	175 mm
Reducing ring Ø	12.7/16/20/22.2/25.4/32 mm
maximum speed	6000 min ⁻¹
Brush width	29 mm
Bore Ø d ₁	50 mm

Type of product

Wheel brush