

**LESSMANN®**  
THE GERMAN BRUSH COMPANY
**Wire wheel brush Steel wire 0.30 / 0.35 mm, Brush Ø D1× bristle width L1:  
 250X30mm**

**Order data**

Order number	570100 250X30
GTIN	4017359079966
Item class	57L

**Description**
**Version:**

Waved wire firmly crimped into the steel body. **High density**, high concentricity, and good wear resistance. Adaptable to various different mounting bores by use of **interchangeable reducing rings** (supplied). Bore with double spline.

**Application:**

Use on bench grinder or polishing machines, or on machines with flexible drive heads. For roughening, cleaning, removing rust, and scale etc.

**Technical description**

Reducing ring Ø	12/12.7/16/20/22.2/25.4/30 mm
Length of brush section H <sub>1</sub>	50 mm
Bore Ø can be opened up to	80 mm
Brush Ø D <sub>1</sub>	250 mm
maximum speed	3600 min <sup>-1</sup>
Brush width	25 mm

Bore $\varnothing d_1$	50.8 mm
Type of product	Wheel brush