

LESSMANN®
THE GERMAN BRUSH COMPANY
**Wire wheel brush Steel wire 0.30 / 0.35 mm, Brush Ø D1× bristle width L1:
 300X35mm**

Order data

Order number	570100 300X35
GTIN	4017359005453
Item class	57L

Description
Version:

Waved wire firmly crimped into the steel body. **High density**, high concentricity, and good wear resistance. Adaptable to various different mounting bores by use of **interchangeable reducing rings** (supplied). Bore with double spline.

Application:

Use on bench grinder or polishing machines, or on machines with flexible drive heads. For roughening, cleaning, removing rust, and scale etc.

Technical description

Bore Ø can be opened up to	100 mm
Brush Ø D ₁	300 mm
Reducing ring Ø	30 mm
Length of brush section H ₁	60 mm
maximum speed	3000 min ⁻¹
Brush width	26 mm

Bore $\varnothing d_1$	50.8 mm
Type of product	Wheel brush