

**Garant**
**DC.T 11T304, Grade: HB7035-1**


### Order data

Order number	260462 HB7035-1
GTIN	4045197874160
Item class	21G

### Description

DC.T 11T304 HB7035-1 Grade: HB7035-1  
 Chip breaker: SM  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.5 - 2.5 mm  
 Feed  $f$ : 0.1 - 0.3 mm/rev.  
 Cutting speed  $v_c$  main application: 100 - 320 m/min

### Technical description

Feed $f$	0.1 - 0.3 mm/rev.
Cutting speed $v_c$ main application	100 - 320 m/min
Cutting depth $a_p$	0.5 - 2.5 mm
Chip breaker	SM
Cutting conditions	heavily interrupted
Main application	P
Corner radius	0.4 mm

Grade	HB7035-1
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	DCMT 11T304
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning