

**LESSMANN®**  
THE GERMAN BRUSH COMPANY**Deburring wheel brush micro-abrasive 1.1 mm, SiC 120, Brush Ø D1× bristle width L1: 250X60mm****Order data**

Order number	570520 250X60
GTIN	4017359258835
Item class	57L

**Description****Version:**

Bore diameter 50.8 mm with double keyway 13×7. Other bore diameters available.

Waved high-tensile **abrasive nylon bristles**.

**Application:**

For all popular bench deburring machines. Particularly long working life due to special wire. Flexible abrasive bristles for even deburring and rounding of corners and surface preparation.

**Note:**

Only the tips of the bristles act on the workpiece. Excessive applied pressure does not improve the result, but increases the required drive power and reduces the working life of the brush.

**Technical description**

Brush Ø D <sub>1</sub>	250 mm
maximum speed	3600 min <sup>-1</sup>
Brush width	58 mm
Length of brush section H <sub>1</sub>	50 mm

Brush material	Silicon carbide grit
Grinding medium code	SiC
Bristle thickness	1.1 mm
Propulsive equipment	Bench deburrer
Type of product	Wheel brush