

LESSMANN®
THE GERMAN BRUSH COMPANY**Wheel brush Steel wire 0.50 mm, Brush Ø D1× bore Ø d1 / thread M:
115XM14mm****Order data**

Order number	571200 115XM14
GTIN	4017359016664
Item class	57L

Description**Version:**

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

Left knotted, reliably avoids premature unwinding.

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards. With **internal thread M14**, for direct mounting **on angle grinders**.

Technical description

Number of twisted knots	20
Brush Ø D ₁	115 mm
Bristle thickness	0.5 mm
maximum speed	12500 min ⁻¹

Length of brush section H ₁	24 mm
Bristle width L ₁	14 mm
Thread M	M14
Brush material	Steel wire
Twisted knotting	left-hand plait
Type of product	Wheel brush