


Garant**SCMT 09T308, Grade: HB7035-1**

Order data

Order number	260763 HB7035-1
GTIN	4045197874436
Item class	21G

Description

SCMT 09T308 HB7035-1 Corner radius: 0.8 mm

Grade: HB7035-1

Chip breaker: SM

Tolerance: M

Cutting depth a_p : 0.5 - 2.5 mm

Feed f : 0.1 - 0.3 mm/rev.

Technical description

Cutting depth a_p	0.5 - 2.5 mm
Corner radius	0.8 mm
Cutting conditions	heavily interrupted
Feed f	0.1 - 0.3 mm/rev.
Main application	P
Grade	HB7035-1
Chip breaker	SM

Cutting speed v_c main application	100 - 320 m/min
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	SCMT 09T308
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning