

**Garant****SNMG 150612, Grade: HB7035-1**

## Order data

Order number	251232 HB7035-1
GTIN	4045197874542
Item class	21G

## Description

SNMG 150612 HB7035-1 Corner radius: 1.2 mm  
Grade: HB7035-1  
Chip breaker: SM  
Cutting depth  $a_p$ : 0.5 - 6 mm  
Feed  $f$ : 0.15 - 0.5 mm/rev.  
Cutting speed  $v_c$  main application: 100 - 320 m/min

## Technical description

Main application	P
Cutting speed $v_c$ main application	100 - 320 m/min
Cutting depth $a_p$	0.5 - 6 mm
Feed $f$	0.15 - 0.5 mm/rev.
Corner radius	1.2 mm
Cutting conditions	heavily interrupted
Grade	HB7035-1

Chip breaker	SM
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	SNMG 150612
Number of changes/inserts	8
Type of product	Indexable insert for turning