

Garant
SNMG 150616, Grade: HB7035-1


Order data

Order number	251332 HB7035-1
GTIN	4045197874566
Item class	21G

Description

SNMG 150616 HB7035-1 Corner radius: 1.6 mm
 Grade: HB7035-1
 Chip breaker: SG
 Cutting depth a_p : 1.5 - 9 mm
 Feed f : 0.25 - 0.8 mm/rev.
 Cutting speed v_c main application: 90 - 260 m/min

Technical description

Grade	HB7035-1
Chip breaker	SG
Corner radius	1.6 mm
Main application	P
Feed f	0.25 - 0.8 mm/rev.
Cutting depth a_p	1.5 - 9 mm
Cutting conditions	heavily interrupted

Cutting speed v_c main application	90 - 260 m/min
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	SNMG 150616
Number of changes/inserts	8
Type of product	Indexable insert for turning