

Garant
SNMM 150616, Grade: HB7035-1


Order data

Order number	251390 HB7035-1
GTIN	4045197874627
Item class	21G

Description

SNMM 150616 HB7035-1 Corner radius: 1.6 mm
 Grade: HB7035-1
 Chip breaker: SR
 Cutting depth a_p : 2 - 12 mm
 Feed f : 0.4 - 1.2 mm/rev.
 Cutting speed v_c main application: 90 - 260 m/min

Technical description

Cutting depth a_p	2 - 12 mm
Grade	HB7035-1
Corner radius	1.6 mm
Cutting speed v_c main application	90 - 260 m/min
Feed f	0.4 - 1.2 mm/rev.
Cutting conditions	heavily interrupted
Main application	P

Chip breaker	SR
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	SNMM 150616
Number of changes/inserts	8
Type of product	Indexable insert for turning