

Garant
VNMG 160404, Grade: HB7035-1


Order data

Order number	251802 HB7035-1
GTIN	4045197874948
Item class	21G

Technical description

Cutting depth a_p	0.5 - 4 mm
Corner radius	0.4 mm
Main application	P
Grade	HB7035-1
Cutting conditions	heavily interrupted
Feed f	0.1 - 0.5 mm/rev.
Cutting speed v_c main application	100 - 320 m/min
Chip breaker	SM
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	VNMG 160404

Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning