

**Garant**
**VNMG 160408, Grade: HB7035-1**


## Order data

Order number	251804 HB7035-1
GTIN	4045197874962
Item class	21G

## Description

VN.G 160408 HB7035-1 Grade: HB7035-1  
 Chip breaker: SM  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.5 - 4 mm  
 Feed  $f$ : 0.1 - 0.5 mm/rev.  
 Cutting speed  $v_c$  main application: 100 - 320 m/min

## Technical description

Cutting conditions	heavily interrupted
Corner radius	0.8 mm
Cutting depth $a_p$	0.5 - 4 mm
Grade	HB7035-1
Cutting speed $v_c$ main application	100 - 320 m/min
Main application	P

Chip breaker	SM
Feed f	0.1 - 0.5 mm/rev.
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	VNMG 160408
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning