

Garant**Mini burr Z7 – medium, diamond cut, Carbide, Type: AF0324****Order data**

Order number	546900 AF0324
GTIN	4045197887870
Item class	51D

Description**Version:**

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank \varnothing 3 mm. With guide face at the tip. Precise deburring without damage to the workpiece.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Toothing grit designation	medium
Overall length	40 mm
Head \varnothing	3 mm
Shape	AF0324

Shape description	Cylindrical with guide face
Type of cut	staggered teeth
Tooth type abbreviation	Z7
Shank Ø	3 mm
Head length	24 mm
Series	#Tooth configuration Z7
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		