

Garant**Burr, Carbide, Type: AF0627****Order data**

Order number	541000 AF0627
GTIN	4045197887863
Item class	51D

Description**Version:**

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Deburring head** with guide face, without cutter at the tip.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Note:

Reduced speed for burrs with an overall length of 120 mm: maximum 11,000 rpm

Technical description

Tooth type abbreviation	Z7
Shank Ø	6 mm
Type of cut	staggered teeth
Overall length	60 mm

Toothing grit designation	medium
Head Ø	6 mm
Shape description	Cylindrical with guide face
Head length	27 mm
Series	#Tooth configuration Z3
Tool material	Carbide
Type of product	Burr