


Garant**WNMG 080404, Grade: HB7035-1**

Order data

| | |
|--------------|-----------------|
| Order number | 252068 HB7035-1 |
| GTIN | 4045197875020 |
| Item class | 21G |

Description

WN.G 080404 HB7035-1 Grade: HB7035-1

Chip breaker: SM

Tolerance: M

Cutting depth a_p : 0.5 - 4 mmFeed f : 0.2 - 0.5 mm/rev.Cutting speed v_c main application: 100 - 320 m/min

Technical description

| | |
|--------------------------------------|---------------------|
| Cutting depth a_p | 0.5 - 4 mm |
| Corner radius | 0.4 mm |
| Cutting speed v_c main application | 100 - 320 m/min |
| Chip breaker | SM |
| Cutting conditions | heavily interrupted |
| Feed f | 0.2 - 0.5 mm/rev. |
| Grade | HB7035-1 |

| | |
|-------------------------------|------------------------------------|
| Main application | P |
| Finishing/roughing assignment | Skrubbearbejdning-sletbearbejdning |
| Tool material | Carbide |
| ISO code indexable insert | WNMG 080404 |
| Number of changes/inserts | 6 |
| Tolerance | M |
| Type of product | Indexable insert for turning |