

LESSMANN®
THE GERMAN BRUSH COMPANY
**Wheel brush with shank Steel wire 0.20 mm, Brush Ø D1× bristle width L1:
 30X6mm**

Order data

Order number	574100 30X6
GTIN	4017359007051
Item class	57L

Description
Version:

Waved special high quality wire, **shank Ø 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

Technical description

Brush Ø D ₁	30 mm
Length of brush section H ₁	6 mm
Bristle thickness	0.2 mm
maximum speed	20000 min ⁻¹
Bristle width L ₁	6 mm
Shank Ø D _s	6 mm
Brush material	Steel wire
Twisted knotting	waved

Type of product

Wheel brush