

**LESSMANN®**  
THE GERMAN BRUSH COMPANY**Wheel brush with shank Brass wire 0.20 mm., Brush Ø D1× bristle width L1:  
70X16mm****Order data**

Order number	574350 70X16
GTIN	4017359007181
Item class	57L

**Description****Version:**

Waved special high quality wire, **shank Ø 6 mm.**

**Application:**

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For heavy-duty deburring and brushing of non-ferrous metals

**Technical description**

Brush Ø D <sub>1</sub>	70 mm
Bristle thickness	0.2 mm
Length of brush section H <sub>1</sub>	19 mm
maximum speed	15000 min <sup>-1</sup>
Bristle width L <sub>1</sub>	12 mm
Shank Ø D <sub>s</sub>	6 mm

Brush material	Brass wire
Twisted knotting	waved
Type of product	Wheel brush