



Spring balance, maximum measuring range: 50N



Order data

Order number	478900 50N
GTIN	4045197208187
Item class	42H

Description

Version:

Sturdy metal housing in practical design; hammer finish. Clear dial face with double scale for measuring in both directions. With pointer and memory pointer.

Application:

For electrical engineering and fine mechanical work, e.g. setting the contact pressure of relay springs, checking the brush pressure on motors or for adjusting tension or compression springs.

Accuracy:

$\pm 0.01 \times (\text{measuring range} + \text{measured value})$.

Calibration: K1

Measuring range: 5 - 50 N

Scale graduations: 1 N

Probe length L: 48 mm

Dial face \varnothing : 72 mm

Technical description

Probe length L	48 mm
Dial face \varnothing	72 mm
Measuring range	5 - 50 N
Scale graduations	1 N
Calibration	K1

Measurement technology	analogue
Type of product	Spring balance

Services

Labelling laser-etched Type	018940
Calibration Spring balance	018870
Calibration Spring balance Type F	027730 F