

Garant**Fleece compact disc, Ø 115 mm, Grit equivalent: 150**

Order data

Order number	566991 150
GTIN	4045197888815
Item class	51M

Description

Version:

Crimped-in fibrous fleece with resin-bonded aluminium oxide grit permits **metal removal and finishing in a single operation.**

Application:

For surface and edge grinding on angle grinders (recommended speed 6000 rpm). **Medium hard** version with **increased aggressiveness and edge stability.** For general deburring work, light removal of material by abrasion with fine surface finish.

maximum circumferential speed: 60 m/s

Bore Ø: 22.23 mm

Grit designation: medium

Degree of hardness: medium

Bore Ø: 22.23 mm

Version: 6 A medium

Technical description

Bore Ø	22.23 mm
Grit equivalent	150
Grit designation	medium

Version	6 A medium
Degree of hardness	medium
recommended speed	6000 min ⁻¹
Disc Ø	115 mm
Iron, sulphur and chlorine constituents	< 0.1 %
Shape description	flat
Product name attribute	Ø 115 mm
optimised for material	Steel
optimised for material	INOX
maximum circumferential speed	60 m/s
Type of product	Compact disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
Plastic, GRP	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		

