



## Cordless 2-speed drill / driver, Manufacturer ID: 71132262

### Order data

Order number	070205 71132262
GTIN	4014586887159
Item class	03F

### Description

#### Version:

#### Cordless drill / driver

- For precise drilling and screw tightening results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Li-ion batteries with high current capability, single-cell monitoring, and capacity display.

#### QuickIN quick-change system.

#### Cordless 2-speed drill / driver

- Low-maintenance POWER-Drive EC DC motor with high torque and overload protection.
- Mechanical torque cut-out adjustable, in 22 steps, additional drilling step.

#### Standard:

- 2-speed cordless drill/driver.
- Short design of 180 mm.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.

#### Supplied with:

2 × 18 V Li-ion batteries, drill chuck, charger, waist clip, transport case.

#### Note:

See No. 073832 for suitable starter kits, spare batteries and chargers.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: Fein type E 18 V

Manufacturer's designation: ABS 18QC

Battery voltage: 18 V

Battery capacity: 2.5 A·h

maximum torque soft: 32 N·m

maximum torque hard: 60 N·m

maximum speed 1st speed: 450 - 550 rpm

## Technical description

Type of product

---

---