



## Cordless 4-speed drill / driver, Manufacturer ID: 71161062

### Order data

Order number	070204 71161062
GTIN	4014586886961
Item class	03F

### Description

#### Version:

#### Cordless drill / driver

- For precise drilling and screw tightening results.
  - Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
  - Sturdy metal gearbox for long working life.
  - Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
  - Li-ion batteries with high current capability, single-cell monitoring, and capacity display.
- Powerful 12V cordless screwdriver with brushless motor with 4-speed gearbox and removable drill chuck.**
- Brushless FEIN power drive motor, powerful and maintenance-free for maximum efficiency and working life.
  - QuickIN quick-change system.
  - Removable drill chuck in all-metal design for outstanding load capacity under the toughest conditions.
  - Optimum cutting speed for every drill diameter, thanks to 4-speed all-metal gearbox.
  - Drill 6 mm holes in metal in 4th gear at 2500 rpm.
  - Powerful thread tapping in 1st gear.
  - Optimum speeds for self-tapping screws, stepped drills or the thread tapping.
  - Compact 150 mm long (without drill chuck).
  - FEIN SafetyCell Technology. Protects the battery and the machine against overheating and deep discharge.
  - Maintenance-free, brushless EC motor with 30 % higher efficiency than DC motors, and high speed stability.
  - Very low wear and up to 10 times the working life compared to standard DC motors.
  - Patented 4-speed gearbox with direct drive for positive screw tightening, drilling at optimised speed, and for thread tapping.

**Mechanical torque cut-out** adjustable in 20 steps, additional drilling step. **Mechanical torque cut-out** adjustable in 20 steps, additional drilling step.

Comprehensive set for drilling, tapping and screwdriving in metal. **Professional thread tapping set** ideal for metalworking.

- **QuickIN bit holder (1/4 inch) with handy one-hand operation and strong Neodymium magnet.**
- **QuickIN tapping adapter with 2 collets for shank diameters 4.5 and 6 mm for cutting threads size M4, M5, M6 / M8.**
- **QuickIN nut spinner adapter for impact nuts with 1/2 inch square drive.**

**Supplied with:**

2 x 12V / 2.5 Ah Li-ion batteries, drill chuck, charger, waist clip, transport case.

Incl. QuickIN 1/4 inch bit holder, QuickIN thread tapping adapter with 2 collets 4.5 and 6 mm, QuickIN 1/2 inch square drive socket

**Note:**

See No. 073832 ff. for suitable starter kits, spare batteries and chargers.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: Fein type E 12 V

Manufacturer's designation: ASCM 12QC

Battery voltage: 12 V

Battery capacity: 2.5 A·h

maximum torque soft: 20 N·m

maximum torque hard: 40 N·m

maximum speed 1st speed: 400 rpm

---

## Technical description

Type of product

---