



## Cordless 4-speed drill / driver, Manufacturer ID: 71161163

### Order data

Order number	070200 71161163
GTIN	4014586887333
Item class	03F

### Description

#### Version:

#### Cordless drill / driver

- For precise drilling and screw tightening results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Li-ion batteries with high current capability, single-cell monitoring, and capacity display.

#### Cordless 4-speed drill / driver with brushless EC motor

- Extremely powerful drill / driver with high concentricity.
- Maintenance-free brushless EC motor with 30% higher efficiency than DC motors, and high speed stability.
- Very low wear and up to 10 times the working life of standard DC motors.
- The high efficiency and the increased battery capacity permit up to 50 % longer operating times.
- Patented 4-speed gearbox with direct drive for positive screw tightening, drilling at optimised speed, together with thread tapping.
- Multi-stage torque setting adjustable in 15 steps, additional drilling step.

With removable **QuickIN quick-change drill chuck** and **carbide-coated jaws**. Comprehensive set for drilling, tapping and screwdriving in metal. **Professional thread tapping set** ideal for the metalworking.

- **QuickIN bit holder (1/4 in)** with handy one-hand operation and strong Neodymium magnet.
- **QuickIN tapping adapter** with 2 collets for shank diameter 4.5 and 6 mm for cutting threads size M4, M5, M6 / M8
- **QuickIN nut spinner adapter** for impact nuts with 1/2 square drive.

#### QuickIN quick-change system.

#### Supplied with:

2 × 18 V Li-ion batteries, drill chuck, charger, waist clip, transport case.

Incl. QuickIN 1/4 inch bit holder, QuickIN thread tapping adapter with 2 collets 4.5 and 6 mm, QuickIN 1/2 inch square drive socket.

**Attention:**

German version. Order free UK adapter plug No. 08 1172\_GB.

**Note:**

See No. 073834 ff and 073845 for suitable spare batteries and chargers.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: Fein type E 18 V

Manufacturer's designation: ASCM 18 QMSET

Battery voltage: 18 V

Battery capacity: 5 A·h

maximum torque soft: 46 N·m

maximum torque hard: 90 N·m

maximum speed 1st speed: 400 rpm

---

**Technical description**

Type of product

---