


## Groove width gauge with intermediate sizes and ISO fits, Type: C



### Order data

|              |               |
|--------------|---------------|
| Order number | 484407 C      |
| GTIN         | 2050001937322 |
| Item class   | 48B           |

### Description

#### IMPORTANT: item is configurable

Nominal size: 9.001 - 12.999 mm, Intervall: 0,001

Tolerance zone: A; B; C; CD; D; E; EF; F; FG; G; H; J; JS; K; M; N; P; R; S; T; U; V; X; Z; ZA; ZB; ZC; ZC

Quality: 10; 11; 12; 13; 7; 8; 9

#### Version:

Groove width gauges with "Go" and "No Go" end. "Go" end with **wear allowance** to DIN 7164.

Gauge body of hardened steel.

For intermediate sizes or numerical tolerances.

Groove width gauge with intermediate sizes and ISO fits, e.g. No. 484407 size **15.8 M6**.

#### Application:

For checking flat fits, e. g. grooves.

#### Standard:

Toleranzen und Abmaße nach **DIN EN ISO 1938-1 und DIN 7164**.

Calibration: L6

Nominal size: 9.001 - 12.999 mm

### Technical description

|                |                   |
|----------------|-------------------|
| Nominal size   | 9.001 - 12.999 mm |
| Tolerance zone | A                 |
| Tolerance zone | B                 |
| Tolerance zone | C                 |
| Tolerance zone | CD                |

|                |    |
|----------------|----|
| Tolerance zone | D  |
| Tolerance zone | E  |
| Tolerance zone | EF |
| Tolerance zone | F  |
| Tolerance zone | FG |
| Tolerance zone | G  |
| Tolerance zone | H  |
| Tolerance zone | J  |
| Tolerance zone | JS |
| Tolerance zone | M  |
| Tolerance zone | K  |
| Tolerance zone | N  |
| Tolerance zone | P  |
| Tolerance zone | S  |
| Tolerance zone | R  |
| Tolerance zone | T  |
| Tolerance zone | U  |
| Tolerance zone | X  |
| Tolerance zone | V  |
| Tolerance zone | ZC |
| Tolerance zone | Z  |
| Tolerance zone | ZA |
| Tolerance zone | ZC |
| Tolerance zone | ZB |
| Quality        | 7  |
| Quality        | 8  |
| Quality        | 9  |
| Quality        | 10 |
| Quality        | 11 |

|                |    |
|----------------|----|
| Quality        | 12 |
| Quality        | 13 |
| Tolerance zone | A  |
| Tolerance zone | G  |
| Tolerance zone | H  |
| Tolerance zone | J  |
| Tolerance zone | K  |
| Tolerance zone | M  |
| Tolerance zone | N  |
| Tolerance zone | P  |
| Tolerance zone | R  |
| Tolerance zone | S  |
| Tolerance zone | B  |
| Tolerance zone | T  |
| Tolerance zone | U  |
| Tolerance zone | V  |
| Tolerance zone | X  |
| Tolerance zone | Y  |
| Tolerance zone | Z  |
| Tolerance zone | A  |
| Tolerance zone | ZB |
| Tolerance zone | ZC |
| Tolerance zone | C  |
| Tolerance zone | D  |
| Tolerance zone | E  |
| Tolerance zone | F  |
| Tolerance zone | CD |
| Tolerance zone | EF |
| Tolerance zone | FG |

|                 |                  |
|-----------------|------------------|
| Tolerance zone  | JS               |
| Calibration     | L6               |
| Type of product | Shaft slot gauge |

## Services

|   |           |
|---|-----------|
| Calibration "Go" / "No Go" plug gauge maximum Ø 20 mm       | 018400 20 |
| DAkKS calibration "Go" / "No Go" plug gauge maximum Ø 60 mm | 019620 60 |
| Labelling laser-etched Type                                 | 018940    |
| Calibration "Go" / "No Go" plug gauge maximum Ø 20 mm       | 028300 20 |
| DAkKS calibration "Go" / "No Go" plug gauge maximum Ø 60 mm | 028340 60 |