



Driven tool, radial, TOEM rail, VX3, Type: 30-VX3-LIK



Order data

Order number	319941 30-VX3-LIK
GTIN	4045197877185
Item class	31W

Description

Version:

For use on **disc turrets**. Left-hand version, i.e. machining in the direction of the main spindle.

Ratio 1:1. Version with internal cooling (internal) max. 70 bar.

For use on all **DMG Gildemeister CTX** CNC lathes with **Sauter** turret. Drive coupling **DIN 5480**.

Clamping of tools in driven tool using ER collet with external nut or VARIA VX quick-change system under license from EWS. External cooling via a coolant tube, internal cooling through the tool centrally through the spindle. Maximum speed 8000 rpm.

Stop rail (42.5 TOEM).

Advantage:

- **Weight- and geometry-optimized design.**
- **Process reliability through high-quality components, longevity.**
- **High torque transmission.**
- **100% control – each driven tool is subjected to a run-in programme.**
- **Internal cooling: specially developed and patented seal.**

Application:

As many machining steps as possible in one clamping set-up. Where space (available clamping positions) in the revolver is at a premium.

Suitable for :

DMG Gildemeister CTX. In some cases, Emco, Hardinge, Monforts, Scherer etc. with DIN 5480.

Supplied with:

Driven tool for collet: including clamping nut and hook spanner. Driven tool VARIA VX: including chuck key.

Optional extras:

Suitable inserts, Varia VX No. 319802 – 319888, ER collets No. 308941 – 309878, ER chuck keys No. 309680 – 309745.

Note:

- **Other drive types (such as DIN 5482), ratios, dimensions, BMT etc. on request, see: www.hoffmann.ews-tools.com**
- **IC tools (with through cooling) will not run dry with standard seal, coolant filtering < 50 µm.**
- **Recommendation: Tighten version VARIA VX with a torque tool (max. 6 Nm).**

VDI size: 30

Tool clamping: Varia VX3

l_1 : 134 mm

b_1 : 695 mm

b_2 : 59.5 mm

h_1 : 68 mm

x: 100 mm

Cooling: internal

Technical description

Cooling	internal
x	100 mm
l_1	134 mm
h_1	68 mm
b_1	69.5 mm
b_2	59.5 mm
Adapter	VX3
VDI size	30
Tool clamping	Varia VX3

Accessories

Indexable drill toolholder VARIA VX3 Clamping range Ø D1 10 mm	319823 10
Axial milling cutter spigot VARIA VX3 Spigot Ø d1 16 mm	319835 16
	319823 16

Indexable drill toolholder VARIA VX3 Clamping range Ø D1 16 mm	
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 6 mm	319823 6
Varia collet chuck VARIA VX3 for ER collets 20 ER	319802 20
Varia collet chuck VARIA VX3 for ER collets 25 ER	319802 25
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 12 mm	319823 12
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 8 mm	319823 8
Varia collet chuck VARIA VX3 for ER collets 16 ER	319802 16
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 20 mm	319823 20
Axial milling cutter spigot VARIA VX3 Spigot Ø d1 22 mm	319835 22
Axial milling cutter spigot VARIA VX3 Spigot Ø d1 27 mm	319835 27
Varia collet chuck VARIA VX3 for ER collets 32 ER	319802 32
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 25 mm	319823 25