

Garant**BMT boring bar toolholder, BMT: 55/E****Order data**

Order number	319888 55/E
GTIN	4045197877451
Item class	31V

Description**Version:**

For internal and external cooling.

High-precision arbors adapted to the specific machine, for flexible use on main and counter-spindle machines. Contact face and functional face ground. Spring-mounted pressure pad for uniform clamping of the turning tools. Perfectly matched for the respective lathe. With secured ball injection nozzles up to 80 bar. Burnished for better corrosion protection.

Application:

For internal machining with boring bar holder or indexable drills.

Technical description

d_a	32 mm
x	85 mm
L_1	64 mm
h_1	85 mm
L_3	22 mm

Z	58 mm
Suitable machines	Emag VL, Emag VT
l_1	115 mm
L_2	64 mm
Type of product	Steel toolholder